



The Alsa Corporation

The World's Most Exotic Finishes

TECHNICAL DATA SHEET

XPOSURES 8 OZ KIT KCXP8K

ALSA CODE	GPI CODE	DESCRIPTION	SIZE
XP-8K	KCXP8K	Xposures 8 oz Kit	8 oz

PRODUCT DESCRIPTION

Xposures® is the first coating of its kind that can be sprayed. Remember the mood ring? Well it is like that but 1 million times better. Xposures® can be sprayed, roller applied, brushed, or even silk-screened. It only reacts to heat and/or sun, and achieves the most dramatic looks over dark bases, especially black.

APPLICATION

1. Begin with a black surface for most dramatic results. (If you need to paint the substrate black, you will need the Xposures® black base sold separately - only applicable if you did not purchase the Xposures® kit.)
2. You will now begin applying Xposures® using very light coats making a few passes until desired results are achieved. **DO NOT** thin the Xposures® material itself. You will simply open up the fluid to the gun further than normal and increase your air pressure (also shake the bottle well prior to pouring). A very easy check to insure adequate coverage is to expose the piece to a source of heat and observe the colour intensity, if more Xposures® is desired simply apply another light coat or two.
3. Let the Xposures® layer completely dry. (Usually within 30 minutes, air dry depending on conditions)
4. Apply the Xposures® U.V. Inhibitor included with your Xposures® purchase beginning with light coats. Allow to dry between coats and re-apply until desired gloss is achieved. The UV Inhibitor can be thinned prior to spraying by using regular **Mineral Spirits** (non-odorless) at a ratio of no more than 20 % (Keep in mind a thinner layer will require multiple coats). Also this UV must be fully dried.
5. Allow to fully dry. (At least 1 - 2 hours, air dry depending on coat thickness is crucial to allow the U.V. Inhibitor to fully dry. This will require baking overnight if necessary to insure it is completely dry to the touch or the final clear will penetrate and kill the Xposures® results.
6. Apply **ALSA KCAC138 Clear** with appropriate Hardener; Use **ONLY** ALSA KCAC138 Clear as any other clear could migrate through the U.V. Unhibitor killing your Xposures® finish.

XPOSURES® KITS (AREA COVERAGE ESTIMATE)

KIT SIZE	COVERAGE
2 oz Kit	Small Appliance (Designed for Evaluation Purposes)
8 oz Kit	A Cruiser / Sports Motorbike
Pint Kit	A Small Car
Quart Kit	A Small to Medium Sized Car



GPI AUTOMOTIVE PRODUCTS P/L
MELBOURNE • SYDNEY • BRISBANE • PERTH • ADELAIDE • LAUNCESTON
FREE CALL 1800 334 898

View GPI's range of products at: www.gpi.com.au/autocart then quote our product code to your supplier for delivery.